


ES SERIES 2- & 3-WAY VALVES



Normally-Closed 2 & 3-Way Electronic Poppet Valves with Side Pin Connector



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
3-way exhaust through top of valve (3-way only)

Order No.

- ES-2S-□ 2-Way Electronic Poppet Valve
- ES-3S-□ 3-Way Electronic Poppet Valve

Normally-Closed 2- & 3-Way Electronic Poppet Valves with Top Pin Connector



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
3-way exhaust through top of valve (3-way only)

Order No.

- ES-2T-□ 2-Way Electronic Poppet Valve
- ES-3T-□ 3-Way Electronic Poppet Valve

Normally-Closed 2- & 3-Way Electronic Poppet Valves with Wire Leads



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)


Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
3-way exhaust through top of valve (3-way only)

Order No.

- ES-2W-□ 2-Way Electronic Poppet Valve
- ES-3W-□ 3-Way Electronic Poppet Valve

Normally-Closed 2- & 3-Way Electronic Poppet Valves with Board Mount



Input Pressure: 28" Hg Vac. to 105 psig
28" Hg Vac. to 50 psig (L)
25" Hg Vac. to 50 psig (H)

Air Flow: 0.6 scfm @ 100 psig
0.5 scfm @ 50 psig (L)
0.45 scfm @ 25 psig (H)

Ports: Inlet and outlet through manifold;
3-way exhaust through top of valve (3-way only)

Order No.

- ES-2B-□ 2-Way Electronic Poppet Valve
- ES-3B-□ 3-Way Electronic Poppet Valve

For Cable and Connectors, see Page 224.